




Preparing a Door Frame for Future Wired Hardware

Single Door - Three Frog Kit
Model No. FRGK-1L2S

EH3 - Electric Hinge



Conduit from FrameFrogs to the ceiling

Conduit connecting FrameFrogs within frame


Recommended Frame Preparation

- Electric Hinge Prep at Center Hinge (3/4" Hole for wires)
- 4.875" x 1.25" DPS Prep in Head with flush cover plate
- Standard Strike Prep
- Omit metal back box (mortar and dust boxes) wherever FrameFrog is installed

Implications for this Layout

- Most flexible configuration with many hardware options available at the strike
- Committed to Electric Hinge for powering the lock
- EPT is not an option
- Adds cost of DPS prep only

EPT3 - Electric Power Transfer



Recommended Frame Preparation

- 9" Long EPT Prep between hinges
- 4.875" x 1.25" DPS Prep in Head with flush cover plate
- Standard Strike Prep
- Omit metal back box (mortar and dust boxes) wherever FrameFrog is installed

Implications for this Layout

- Flexible configuration with limited space for some hardware options at the strike
- Committed to EPT for powering the lock
- Electric Hinge is not an option
- Adds cost of DPS and EPT prep

☐ EH3













☐ EPT3

Select the box to indicate the configuration to use for frames without electrified hardware



Single Door Kit Contents

Model No.
FRGK-1L2S

FrameFrog Long FRG4L	1	
FrameFrog Short FRG4S	2	
1/2" PVC Conduit - 40" Long	3	
1/2" PVC Sweep elbows - 4" R	2	
Weld Clips (Suffix WC) Wing Tabs (Suffix WT) Epoxy for FRP (Suffix EPOX)	See Images	 x6  x6  x2
PVC connectors	1	
1/2" EMT connector	1	
3/4" EMT connector	1	
Threaded 1/2" PVC Connector	1	
QR code door labels	1	

2026.1

Common Configurations

Consult Hardware Specialist For Other Configurations And Implications